
Airofog Gel Gun is designed by the theory of negative pressure. Gel bait is sucked out through the gun instead of being pushed out in the traditional way by a plunger, ensures an accurate amount of each bait placement and avoids an overflow of gel bait. By adjusting the wheel regulator, 5 different doses can be selected to meet a variety of demand. Adapts to most 30g/35g gel cartridges.

Safety

- Keep out of reach of children.
- Never inject the metal tip/needle of the gun into electric outlets.
- Not to touch the exposed cables or electric outlets with the gun's metal part especially in the thunder weather.
- Follow the manufacturer's instruction for the safety of gel cartridge.

Getting Started

Step 1: Remove the closure (18) and place a stainless steel or plastic needle (19).

Step 2: Remove the tip cover of gel cartridge, then insert the cartridge into the gun compartment by pushing it against the piston (12) until the base of cartridge is seated well on the top hook of the trigger (3).


Step 3: Adjust the regulator (4) to position 5. Push the gel bait plunger gently from the base of the cartridge to drive the gel to the outlet, then press repeatedly the trigger until the gel comes out.

Step 4: Now the gun is ready for application.


Step 5: Dial the regulator to the position from 1 to 5 to get the desired dose.

Step 1 ~ 5


(1)




(2)




(3)



(4)




(5)



After using

- Take off the needle (19) from the gun, screw back the closure (18) to the gun to prevent the drying of gel at the output.
- Dial the regulator to “0” position to avoid trigger pressing by accident.
- Leave the gel cartridge into the gun compartment to prevent the gel left inside the gun from drying then blocking the piston and other gun parts.
- If necessary, clean the used needles with the cleaning rod.
- Put the gun and parts back into the provided pouch .



Attention

Dosage performance varies depending on viscosity and density of the gel used. Airofog Gel Gun provides 2 types of wheel regulator - smaller dosage (red) and bigger dosage (black) with a remark of “B” on the wheel. It is recommended to do a test prior to parameterize adjustment.

Airofog Gel Gun is only for gel bait, not for application of high viscosity pastes.

Dosage reference

regulator mark	red (smal)	black (big)
1	0.017g	0.05g
2	0.033g	0.1g
3	0.05g	0.15g
4	0.067g	0.17g
5	0.083g	0.19g